



WIRING DIAGRAM FOR THE 37500 & 37520

- ⚠ Reverse Devices:**
N.O. contact of Safety-Edge(s)
* Second contact optional
(Special Software)



DIP Switch: shown in default position. Set as required by sliding/depressing actuators ...

- ⚠** - Set DS1 to Auto when Remote switch used
P1 - Set Green Light time 0 - 180 secs.
P2 - Set Wait time (after Green Light) 1 - 180 secs.
Pr1 - Plug for Optional Remote Control Receiver
U5 - WiFi Interface * Antenna Connector



DEVANCO CANADA

For more information, please call toll free at 855-931-3334